

## Flip Seal Plugs and Connectors, 10-50P



**Model #:** P1050DF  
**Volts:** 125/250 VAC  
**Max Amps:** 50 Amps  
**Pole/Wire:** 3 Pole 3 Wire  
**Blade Type:** Straight  
**NEMA:** 10-50P

KH Flip Seal wiring devices are industrial grade and feature KH's exclusive Flip It & Forget It™ plug and connector design which seals out dust, dirt, and moisture.

KH Flip Seals are used in agriculture, manufacturing, and industrial applications. When the connector's 'lip' is flipped over the plug a secure electrical connection is made; if the plug is tugged it will stay connected. To safely disconnect, just give it a hard pull.

- Industrial grade, extremely durable design and construction.
- Re-wireable design.
- Rubber housing with phenolic insert provides rugged and durable construction.
- Molded rubber lip on connector provides a moisture, dust, and weather resistant enclosure when flipped over the plug.
- Stainless steel screws.
- Available in straight or locking blade, 15-, 20- and 50-Amperage.
- Made in the U.S.A.