



## 65940-962: One Light Pendant



**Collection:** Windgate

One Light Pendant in Brushed Nickel Finish with Alabaster Glass Shade

**UPC #:**785652020278

**Finish:** Brushed Nickel (962)

### Dimensions:

**Diameter:** 13 1/4"

**Height:** 9"

**Overall Height:** 47 1/4"

**Wire:** 72" (color/Clear Silver)

**Chain:** 36"

**Mounting Proc.:** Center Lock-Up

### Bulbs:

- 1 - Medium A19 150w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

### Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

### Material List:

- 1 Body - Steel - Brushed Nickel
- 1 Chain - Steel - Brushed Nickel

### Safety Listing:

- Safety Listed for Dry Locations
- Safety Listed for Dry Locations

### Instruction Sheets:

Bilingual (English - French) (HC-1697FB)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Alabaster	1				5 3/8	13 3/4	1 5/8			

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	7/8			5		

### Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	65940-962	1	785652020278	15.25	7.5	15.5	1.026	5.6	150	Yes
NJ Pallet		66		48	40	73	81.111	369.9		No
NV Pallet		66		48	40	73	81.111	369.9		No