



Search within category

BUY NOW

DESIGN / INSTALL



LDPH3IW8-A

Tamper resistant two-piece latching surface raceway. Supplied with pre-punched mounting holes and factory applied adhesive tape. Available in 6', 8', and 10' lengths, Off White, PVC, Length 8.00 ft, Width 0.77 in.

Specs Packaging Details Documents

★ Add to Favorites

🛒 Add to BOM

Product Type	Raceway
Color	Off White
CSA 22.2 No.62-93	Yes
UL5A Listed	Yes
Height (In.)	0.41
Length (ft.)	8
Width (In.)	0.77
CE Compliant	Yes
Depth (In.)	0.41
Depth (mm)	10.4
Fitting Type	Raceway
Height (mm)	10.4
Length (In.)	96.0
Length (m)	2.4
Length (mm)	2438.4
Length ft. (m)	8 (2.4)
Material	PVC
Mounting	Adhesive/Screw On
Mounting Holes	false
Part Features	Tamper resistant two-piece latching surface raceway. 0.75" x 0.41" (20.0mm x 10.4mm). Two-piece hinged design allows cables to be laid in. Factory applied adhesive backing speeds installation. Terminates using surface mount outlet box solutions or Panduit Mini-Com Surface Mount Boxes.
Product Length	8'
Product Size	3
Raceway Size	0.77" x .41" (20.0mm x 10.4mm) (20.0mm x 12.0mm) (20.0mm x 10.4mm)
Width (mm)	20.0
RoHS Compliancy Status	Compliant
Min. Order Qty.	160.0000

Request a Quote
 Are you looking for a free quote on Panduit Products and Solutions?
 Yes, I need a quote! ▶

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)

Request a Quote
Are you looking for a free quote on Panduit
Products and Solutions?

Yes, I need a quote! ▶