

WB1451ORB: 1 - Light Sconce



Dimensions:

Width: 5" **Extends:** 4"
Height: 14 3/4" **Mounting Proc.:** Set Screw(s)
Weight: 3.6 lbs. **Connection:** Mounted To Box

Bulbs:

1 - Medium T10 60w Max. 120v - Not included

Features:

- Meets American with Disabilities Act standard extension requirements
-

Material List:

1 Body - Steel - Oil Rubbed Bronze

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

English (WB1451)

Collection: Mila

UPC #: 014817372007

Finish: Oil Rubbed Bronze (ORB)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Glass	White Opal Etched	1			4	12 1/2					

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	14	5			7	7 3/4

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	WB1451ORB	1	014817372007	17	8	8	0.63	4.9	125	Yes

Master Pack		2	10014817372004	17.5	17	9	1.549	11.7	125	Yes
NJ Pallet		80		48	40	74	82.222	468		No
NV Pallet		80		48	40	72.5	80.556	448		No