

Stratmoor 52" Collection

52 Inch Stratmoor Fan BSS

339022BSS (Brushed Stainless Steel)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____



Product Information

Product ID	339022BSS
Finish	Brushed Stainless Steel
Blade Finish	Medium Oak/Dark Oak
Collection	Stratmoor 52" Collection

Airflow, Power and Efficiency

Speed	RPM	CFM	CFM/ Watt	Amps	Watts
High	160	4830	82	.49	59
Med	110	3323	119	.35	28
Low	63	1779	187	.2	10


Specifications

Number of Blades	5
Blades Included	Yes
Blade Pitch	14 Degrees
Blade Sweep	52"
Blades Reversible	No
Blade Material	WOOD
Optional Blades Available	No
Downrod 1	FLUSH MOUNT

Primary Control System
 Pull Chain - In project applications using multiple ceiling fans, alternative remote controls may be required. Please contact Kichler Advanced Product Solutions at 844-542-4537 to confirm your project requirements.

Remote Included	No
Wall Control Included	No
Low Ceiling Adaptable	Yes, Low Ceiling Adaptable
Lead Wire Length	12.00"
Motor Size	153MM X 15MM
Motor Type	AC

Dimensions



Downrod	A	B	C	D
FLUSH MOUNT	8.25	6.75	11.50	11.00

Downlight

Watts	59/28/10
Optional Light Kit Available	Yes

Available Finishes

Finish	Fixture	Glass	Blade 1	Blade 2

Safety Listings & Certifications

Safety Rated	Dry
--------------	-----

Stratmoor 52" Collection
52 Inch Stratmoor Fan BSS
 339022BSS (Brushed Stainless Steel)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____

Finish	Fixture	Glass	Blade 1	Blade 2
Brushed Stainless Steel	339022BSS	N/A	MEDIUM OAK	DARK OAK
Oil Brushed Bronze	339022OBB	N/A	WALNUT	CHERRY
White	339022WH	N/A	WHITE	WHITE
Matte White	339022MWH		MATTE WHITE	MATTE WHITE

Warranty www.kichler.com/warranty

Installation

Installation requirements The electrical junction box and support structure must be securely mounted and capable of reliably supporting a minimum of 50 pounds. Use only ETL/UL listed electrical junction boxes marked "For Fan Support"

Electrical Requirements 120V 60Hz AC
 Hanging Weight 14.4 LBS
 Minimum Distance Between Bottom Of Fan Blade To Floor 7.5 feet

Control Options

Product ID	Descr
337001WH	Universal Remote Control
337012ALM	4 Speed Fan Slide Control
337012IV	4 Speed Fan Slide Control
337012WH	4 Speed Fan Slide Control
337214	Limited Function Cooltouch
370039MUL	Wall Control System L-Function
370040	4 Speed Rotary Switch 10 AMP
3R400BSS	CoolTouch Control System R400