

Product availability : Stock - Normally stocked in distribution facility



Price* : 413.00 USD



Main

Product or component type	Miniature circuit-breaker
Range of product	Homeline
Line Rated Current	50 A
Product certifications	UL listed
System Voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	2P
Short-circuit current	10 kA
Number of spaces required	2
Circuit breaker type	Ground fault protecting class A 6 mA
Circuit breaker application	HACR rated
Electrical connection	Screw clamp terminals
AWG gauge	AWG 12...AWG 4 for 1 cable(s) (aluminium) AWG 14...AWG 6 for 1 cable(s) (copper)
Height	3.13 in
Width	2 in
Depth	2.98 in

Ordering and shipping details

Category	00147 - HOM 2 POLE GFI CB,40A MAX
Discount Schedule	DE3D
GTIN	00785901783572
Nbr. of units in pkg.	1
Package weight(Lbs)	1.21
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1340 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	Lifetime
-----------------	----------