



Actual

Catalog Number: RB44
Product ID: 7TAI029690R0013
UPC Number: 78621080430
EAN Number: 05414363158608
Status: Active

Nylon Insulated Crimp-On Wire Joint, Length .78 Inches, Width .31 Inches, Wire Range 2#18 - 2#16, Color White

- Application Tools: WT2000

North American Specifications (UNSPSC)

UNSPSC	39121452 Cable joint
IGCC	4677 Cable joint
Brand Name	Sta-Kon
Type	Wire Joint
Application	Provides terminating point for a group of wires running in one direction.
Standard	UL E9809
Material	Nylon
Finish	Tin Plated
Color	White
Temperature Rating	to 221 Degrees F (105 Degrees C)

Packaging

Inner Quantity	100
Inner Dimensions (inches)	1.25x2.5x3.5
Outer Quantity	500
Outer Dimensions (inches)	2.688x7.125x3.75
Weight Uom	2.5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com