


# MONORAIL

## MonoRail T20

### DESCRIPTION

Low-voltage conductor of two individual conductive metal pieces fused together by a plastic separator. Hand-bendable, field-cutttable MonoRail is rated for 300 watts at 12 volts, 600 watts at 24 volts. Each piece of rail is shipped with conductive connectors to join rail pieces end to end. Order additional connectors if cutting and rejoining rails. Standard



### WEIGHT

0.27-1.1lb / 0.12-0.5kg ±

brown



### ORDERING INFORMATION

700MOA SHAPE OR SIZE	LENGTH (A)	COLOR	FINISH
STRAIGHT	24 24"	BR BROWN CLEAR	Z ANTIQUE BRONZE
	48 48"		S SATIN NICKEL
	96 96"		



**TECH LIGHTING®**  
 7400 Linder Avenue      T 847.410.4400  
 Skokie, Illinois 60077      F 847.410.4500

**Tech Lighting, L.L.C.**

700MOA \_\_\_\_\_

FIXTURE TYPE: \_\_\_\_\_

JOB NAME: \_\_\_\_\_

NOTES: \_\_\_\_\_

\_\_\_\_\_

\_\_\_\_\_