



Actual

Catalog Number: TY2X3NPG6
Product ID: 7TAA104040R0087
UPC Number: 78621095711
Status: Obsolete
Replacement Catalog: TYD2X3NPG6

Wiring Duct Narrow Slot 2 Inch X 3 Inch Rigid PVC Gray

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Brand Name	Ty-Duct
Type	Wiring Duct
Special Features	Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
Width	2.25
Depth	3.14
Length	6
Mounting Holes	Yes
Material	Rigid PVC
Color	Gray

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	77.5mm
Width	57.2mm
Length	1829mm
Halogen free	Y
Type of fastening	Adhesive film
With cover	N
Colour	Light grey

Packaging

Inner Quantity	6
Outer Quantity	60
Outer Dimensions (inches)	73x9x6.5
Weight Uom	40.63 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000181

For further technical assistance, please contact us...

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com