



Siemens Low Voltage Residential Circuit Breakers Miniature Thermal Mag Circuit Breakers - Duplex, Triplex, Quadplex are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: QT Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240 V Amperage Rating: 20-30A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: Two single poles and one double pole

Suitability for operation	Electrical Distribution
Model	
Product brand name	SIEMENS
Type of electrical connection	PLUG-IN
Mechanical Design	
Depth [in]	3 in
Design of the product	QT
Height [in]	2 in
Width [in]	3 in
General product approval	
Standard	UL 489
last modified:	04/24/2020