

FM272BS: 2 - Light Indoor Flush Mount

Dimensions:

Diameter: 14" **Wire:** 8"
Height: 5 1/4"
Weight: 11.5 lbs.

Bulbs:

2 - Medium A19 60w Max. 120v - Not included

Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
-

Material List:

1 Body - Steel - Oil Rubbed Bronze

Safety Listing:

Safety Listed for Dry Locations
 Safety Listed for Dry Locations

Instruction Sheets:

English (FM272)



Collection: Barrington

UPC #: 014817330823

Finish: Brushed Steel (BS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Etched Glass	Opal Etched	1				12 1/2	12 1/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Mounting Plate	1	4				

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	FM272BS	1	014817330823	17	18.5	8.75	1.593	10	125	Yes

Master Pack	FM272BS	2	10014817330820	17	18.5	17.5	3.185	20	125	Yes
NJ Pallet		32		48	40	74	82.222	320		No
NV Pallet		32		48	40	74	82.222	320		No