



Powering Business Worldwide

pe.eaton.com

Type BR 1-inch Plug-on Circuit Breaker

BR120

UPC: 786676362108

Dimensions: 2.5 IN * 1 IN * 3 IN (L * W * H)

Notes: No Data

Warranty: Limited lifetime residential, 1 year commercial

Specifications:

- **Type:** Thermal magnetic circuit breaker
- **Mounting:** Plug-on
- **Main Circuit Breaker:** BR
- **Wire Size:** #14-4 AWG Cu/Al at 60°C or 75°C
- **Quantity:** 1
- **Used With:** Type BR loadcenters
- **Amperage Rating:** 20A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V

Supporting documents:

- [Retail Catalog Brochure](#)
- [Eatons Volume 1-Residential and Light Commercial Catalog](#)
- [Eaton Specification Sheet - BR120 Specification](#)
- [Type BR, BD, BQ, BQC, BRH, GFCB, GFCBH, 10-70Amp 1-Pole - Curve Line Drawing](#)

Certifications:

- UL 489

Product compliance:

- Federal Specifications Classification W-C375



