



Tilo™ - CF130

- CF130BS - Brushed Steel Housing, Dark Cherry Blades
- CF130WW - Appliance White Housing, Appliance White Blades
- CF130ORB - Oil Rubbed Bronze Housing, Dark Cherry Blades


- 30" blade span
- Light fixture adaptable (LK130 sold separately)
- 4.5" downrod included
- Three curved blades
- Dual-mount feature
- Damp Location (BS not recommended for outdoor use)
- Ships to Canada



SW46 Wall Control

Energy Information at High Speed

Airflow	Electricity Use	Airflow Efficiency
2278	42	54
<small>Cubic Feet Per Minute</small>	<small>Watts (Excludes Lights)</small>	<small>Cubic Feet Per Minute Per Watt</small>



A: 9.5"/13.3" B: 8.1"/11.9" C: 7.3" D: 5.1"

moving air in style.