



S8406

F17T8/841/ENV
17 watt; T8; Fluorescent; 4100K Cool White; 85 CRI; Medium Bi
Pin base



Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8406

Item Number	Product Line	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code
S8406	HyGrade	045923084065	17	T8	Medium Bi-Pin	G13	F17T8/841/ENV
MOD In Inches	MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color
1.00"	23.78"	24"	1450	1350	20000	4100	Cool White
Pack	CRI	Hg Content	RoHS Compliant				
30	85	3.5 mg	Yes				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

