

Item # 8690-66	UPC Code: 747396078755
Product Family Name: Harrison™	Finish: Black
Category: WALL MOUNT	Category Type:
Certification 3187291	
Patents:	
Notes:	



Image File Name: 8690-66.jpg



MEASUREMENTS

Width: 6.25	Length: 11.5	Height: 7.75	Extension: 7.75
Height Adjustable: No	Min Overall Height: No	Max Overall Height: No	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 3.73
Canopy Width: 5.5	Canopy Height: 7.13	Canopy Length:	Center to Bottom: 6.75
Backplate Width:	Backplate Height:	Center to Top: 4.75	

LAMPING

No. of Bulbs: 1	Light Type: A19 MED			
Max Bulb Wattage: 100	Socket: E26 MED			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included: No	Bulb/LED Included:
Bulb/LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description: Clear Beveled Glass	Material: Glass
Part No.: G8690A	Quantity: 8
Width:	Height:
	Length:



SHIPPING

Carton Width: 8.5	Carton Height: 14.25	Carton Length: 10.5
Carton Weight: 4.928	Carton Cubic Feet: 0.736	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1



**Wet
Location**



**ETL
Intertek**