

Eaton Type CH circuit breaker surge protective device

CHSPT1ULTRA

UPC:786685436821

Dimensions:

- Height: 1 IN
- Length: 1 IN
- Width: 1 IN

Weight:.93 LB

Notes:20kA nominal discharge current. Has 50kA one time surge current rating.

Warranties:

- 1 year

Specifications:

- **Type:** Type 1
- **Frequency Rating:** 50/60 Hz
- **Interrupt Rating:** 200 kAIC
- **Operating Voltage:** L-L 300, L-N 150
- **Maximum Continuous Operating Voltage (MCOV):** 150 V L-N, 300 V L-L
- **Short Circuit Current Rating (SCCR):** 200kA
- **Nominal discharge current 8x20us (In):** 20kA
- **Voltage Protection Rating (VPR):** 1000 V L-L, 600 V L-N
- **Voltage Rating:** 120/240V
- **Enclosure:** NEMA 4
- **Phase:** Single-phase
- **Surge Current:** 50kA

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [CHSP Type 1 Surge Protective Devices](#)
- [Type 1 Surge Protective Devices](#)
- [Eaton Specification Sheet - CHSPT1ULTRA](#)



Certifications:

- UL 1449

Product compliance: No Data

© 2016 Eaton. All rights reserved.