


LEDTASK™ FLEXIBLE WET LOCATION LED RIBBON 12VDC STANDARD OUTPUT - 39" (1M), 16'-4" (5M) REELS



PRODUCT DESCRIPTION

A wet location flexible LED linear ribbon that conforms to straight, curved and irregular architectural coves, outdoor steps and bannisters, fountain exteriors, outdoor cooking islands and food stations, recesses, and other constructs where even, energy saving LED illumination is specified in environments that are exposed to moisture. **Not to be submerged directly in water.** Available in a 39" (1M) and 16'-4" (5M) reel. Ribbon can be cut and sealed in the field to achieve desired length.

Custom lengths available - consult factory

Aluminum architectural mounting channels available - consult website: www.gmlighting.net

PROJECT	TYPE
CATALOG NUMBER	

KEY FEATURES

- Flexible wet location LED ribbon that is cuttable in the field (do not submerge)
- Fully surrounded in moisture resistant acrylic linear sheath
- Achieve virtually any location custom installation where moisture may be present
- Comes with mounting clips, silicone sealant and end caps
- Flexible ribbon to ribbon and ribbon to power supply connectors available (see below)
- Dimmable

ELECTRICAL


- 12VDC
- Rated at 1.52W per foot
- 39": 0.4A / reel, 16'-4": 2A / reel
- 19 LED's per foot, .08W each
- 50,000 hr. LED life

OPTICS

- 2700K, 3000K, 3500K, 4200K, 5500K
- Up to 153 lumens per foot

LABEL

- ETL



FIXTURE ORDERING INFORMATION

Catalog No.	Length	Wattage	Total Amps	Lumens	Color Temp.*
LTR60WP-S0-27	39" / 1M	.08W (1.52W/ft.)	0.4A	111/ft.	2700K
LTR60WP-S0-30	39" / 1M	.08W (1.52W/ft.)	0.4A	115/ft.	3000K
LTR60WP-S0-WW	39" / 1M	.08W (1.52W/ft.)	0.4A	134/ft.	3500K
LTR60WP-S0-42	39" / 1M	.08W (1.52W/ft.)	0.4A	144/ft.	4200K
LTR60WP-S0-PW	39" / 1M	.08W (1.52W/ft.)	0.4A	153/ft.	5500K
LTR300WP-S0-27	16'-4" / 5M	.08W (1.52W/ft.)	2.0A	111/ft.	2700K
LTR300WP-S0-30	16'-4" / 5M	.08W (1.52W/ft.)	2.0A	115/ft.	3000K
LTR300WP-S0-WW	16'-4" / 5M	.08W (1.52W/ft.)	2.0A	134/ft.	3500K
LTR300WP-S0-42	98'-6" / 30M	.08W (1.52W/ft.)	2.0A	144/ft.	4200K
LTR300WP-S0-PW	98'-6" / 30M	.08W (1.52W/ft.)	2.0A	153/ft.	5500K

CONNECTOR ORDERING INFORMATION

Cat. No.	Description
LTCWP-12	12" flexible ribbon to ribbon connector
LTCWP-24	24" flexible ribbon to ribbon connector
LTCWP-36	36" flexible ribbon to ribbon connector
LTCWP-60	60" flexible ribbon to ribbon connector
LTW-24-WP	24" flexible ribbon to power supply connector
LTW-48-WP	48" flexible ribbon to power supply connector
LTW-60-WP	60" flexible ribbon to power supply connector
GMSB-W	Splice box - white 2"L x 1"W x 5/8"D
GMSB-B	Splice box - black 2"L x 1"W x 5/8"D
WPKT	Waterproof accessory kit

NOTE: Each 39" reel includes: (1) female wet location ribbon to power supply connector (LTW-24-WP), 6 silicone mounting clips, 12 stainless steel screws, 2 silicone end caps, 1 male plug for plugging end of run and a tube of silicone sealant.

Each 16'-4" reel includes: (1) 24" female wet location ribbon to power supply connector (LTW-24-WP), 20 silicone mounting clips, 40 stainless steel screws, 2 silicone end caps, 1 male plug for plugging end of run and a tube of silicone sealant.

* Kelvin temperature (color) ±200K

POWER SUPPLIES: GM offers a complete line of power supplies. Please see our website at www.gmlighting.net

PHOTOMETRICS: Photometric reports and .ies files are available. Please consult product page on website at www.gmlighting.net