



S2977

40T8
40 watt T8 Incandescent; Clear; 2000 average rated hours; 265 lumens; Medium base; 130 volts

Features

- Special application incandescent
- Not for Enclosed Fixtures
- Horizontal Burn Only
- Showcase use
- 130 volt



S2977

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|-----------------------|---------------|-------------------------------|------------|----------------|---------------------|-----------|--------------|
| S2977 | 045923029776 | 40 | T8 | Medium | E26 | 40T8 | 130 |
| Finish | MOL In Inches | MOD In Inches | Filament | Initial Lumens | Average Rated Hours | Pack | Package Type |
| Clear | 12" | 1.00" | C-8 | 265 | 2000 | 250/25 | Box |
| Dimmable/Non-Dimmable | | CEC Status | | | RoHS Compliant | | |
| Dimmable | | Lawful for sale in California | | | Yes | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

