



Item #: **F701-DRB**
 Product Family Name: **Delano®**
 Category: **Interior Fan**
 Certification: **E75795**
 Patents:
 Notes:

UPC Code: **706411029783**
 Finish: **Dark Restoration Bronze™**
 Category Type: **Ceiling Fan**

Image File Name:
 F701-DRB--
 1509648453.jpg



MEASUREMENTS

Blade Finish:			Reversible Blades:	No
Blade Material:	Plywood Construction		Slope:	No
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:	27.56
52	5	14 degrees		
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:	
6	0.75			
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:	
15.50	8.75	80	172x20mm	

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	65		100		160
Amps:	0.35		0.47		0.59
Watts:	17.000		35.000		72.000
CFM:	2064.38		3293.00		5278.32
CFM/Watts:	121.43		94.09		73.31



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	Yes
	Included Remote Control:	Included Wall Control:
		WCS213
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	RCS213	

LAMPING

No. of Bulbs:	Light Type:			
2	Mini-Can Halogen			
Max Bulb Wattage:	Socket:			
50	E11			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
Yes	Yes			Y
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes	3			

GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
GF701-1	1
Width:	Height:
	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
15.000	12.380	25.500	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
28.860	2.740	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
		1	1



Title 17

Yes



UL Listed

Yes