



## Specification Sheet

# Commercial Service<sup>®</sup>

# A23 General Purpose Incandescent Lamp

Order Number **04543**

## Specifications

Energy Used (Watts).....	200
Domestic Code.....	200A23/130
Volts.....	130
Brightness (Lumens) .....	3850
Average Rated Hours .....	750
Life (in years)* .....	0.7
Dimmable.....	Yes
Filament Type .....	CC6
Light Center Length (LCL) .....	4"
Estimated Yearly Energy Cost** .....	\$24.09
Country of Origin.....	China

## Physical Characteristics

Finish.....	Clear
Base.....	Medium
MOL.....	5 1/2"



\* Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com)

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee  
©“Westinghouse” and “You can be sure...if it’s Westinghouse” are all registered trademarks of Westinghouse Electric Corporation

