



### 41162-05: Three Light Wall / Bath



#### Dimensions:

**Width:** 20" **Extends:** 5 1/2"  
**Height:** 8 1/2" **Wire:** 6 1/2"  
**Weight:** 4 lbs.

#### Bulbs:

3 - Medium A19 100w Max. 120v - Not included  
 3 - LED Medium A19 8w Max. 120v - Not included  
 3 - LED Medium A19 13.5w Max. 120v - Not included

#### Features:

- Easily converts to LED with optional replacement lamps
- Fixture may be mounted in the up or down position
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

#### Material List:

1 Body - Steel - Chrome

#### Safety Listing:

Safety Listed for Damp Locations  
 Safety Listed for Damp Locations

#### Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1899FS)

**Collection:** Oslo

**UPC #:**785652171512

**Finish:** Chrome (05)

#### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Cased Opal Etched	3				5 29/32	3 15/16				

#### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	4 3/4	8	13/16		6 1/4	2 1/4

#### Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

#### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	41162-05	1	785652171512	21.5	11.5	6.5	0.93	4.9	150	Yes
NJ Pallet		66		48	40	77	85.556	323.4		No
NV Pallet		66		48	40	77	85.556	323.4		No