



Powering Business Worldwide

pe.eaton.com

Series C, F-frame Molded Case Circuit Breaker

ED3020

UPC:782116303939

Dimensions:

- **Height:** 6 IN
- **Length:** 3.38 IN
- **Width:** 4.13 IN

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 20A
- **Interrupt Rating:** 65 kAIC at 240 Vac
- **Number Of Poles:** Three-pole
- **Frame Size:** F-frame
- **Series:** Series C
- **Trip Type:** Fixed thermal magnetic

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [FD3 2D PDF](#)
- [FD3 3D Model Xchange](#)
- [Counterfeit and Gray Market Awareness Guide](#)
- [MOEM MCCB Product Selection Guide](#)
- [Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)
- [Time Current Curves for Series C® F-Frame Circuit Breakers](#)
- [F-Frame 310+ Molded-case circuit breakers 15-225A](#)
- [F-frame Molded Case Circuit Breaker Drawing](#)
- [FD3 3D Inventor](#)



- [FD3 2D Drawing Xchange](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.