



Powering Business Worldwide

pe.eaton.com

Series G, EG-frame Molded Case Circuit Breaker

EGB3030FFG

UPC:782114876312

Dimensions:

- **Height:** 5.5 IN
- **Length:** 2.99 IN
- **Width:** 3 IN

Weight:3 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 30A
- **Interrupt Rating:** 25 kAIC at 240 Vac, 18 kAIC at 480 Vac
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600Y/347V
- **Mounting Hardware:** Metric
- **Frame Size:** EG-frame
- **Series:** Series G
- **Terminals:** Line and load
- **Trip Type:** Fixed thermal, fixed magnetic

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Series G Molded Case Circuit Breakers - Quick Selector](#)
- [EG-Frame Circuit Breaker 15-160 Amperes Technical Data](#)
- [EG-frame Molded Case Circuit Breaker Drawing](#)



- Eaton Series G type EGB, EGE, EGS, EGH, EGC, and EGK circuit breakers
- MOEM MCCB Product Selection Guide

Certifications:

- IEC Rated
- CSA Certified
- UL Listed

Product compliance:

- CE Marked