

# TCR20-T



UPC Code: 07847765536

Country Of Origin: Mexico

\*Eligible for ARRA funded projects > \$7,443,000



# TCR20-T

## Brand Features

Plug Into Safety with Leviton Tamper-Resistant (TR) Receptacles. As a long-time manufacturer of tamper-resistant devices, we are pleased to be at the forefront of this safety measure with an expanded product line that encompasses a wide range of TR devices in Residential, Commercial, Industrial and Hospital Grades.

The National Electrical Code® mandates the use of tamper-resistant receptacles in various applications, and has expanded the usage requirements over the course of several code cycles. To see which version of the National Electrical Code your State or Locality has adopted, [please click here](#).

## Item Description

20 Amp, 125 Volt, NEMA 5-20R, 2P, 3W, Tamper-Resistant, Narrow Body Duplex Receptacle, Straight Blade, Commercial Grade, Self Grounding, Side Wired, Steel Strap - LIGHT ALMOND

## Technical Information

### AC Horsepower Ratings

**Horsepower Rating:** 1 HP

### Electrical Specifications

**Dielectric Voltage:** Withstands 2000V per UL498

**Grounding:** Self-Grounding

**Temperature Rise:** Max 30C after 100 cycles OL at 150 percent rated current

**Voltage:** 125 Volt

**Amperage:** 20 Amp

**Current Limiting:** Full Rated Current

**Wire:** 3

**Pole:** 2

### Environmental Specifications

**Operating Temperature:** -40C to 60C

**Flammability:** Rated V-2 per UL94

### Material Specifications

**Strap Material:** Zinc-Plated Steel

**Body Material:** Thermoplastic

**Face Material:** Thermoplastic

**Ground Clips:** Brass

**Terminal Screws:** Plated Steel

**Shutter Mechanism:** Delrin® Acetal

**Line Contacts:** Brass .031 Thick

**Grounding Screw:** Plated Steel

### Mechanical Specifications

**Product ID:** Ratings are permanently marked on device

**Wire Type:** Solid or Stranded Building Wire

**Terminal ID:** Brass-Hot, Green-Ground, Silver-Neutral

**Termination:** Side

**Terminal Accom.:** 10-14 AWG

### Product Features

**Color:** Light Almond

### Standards and Certifications

**cULus:** File E13399

**ANSI:** C-73

**NOM:** 057

**NEMA:** WD-1 & WD-6

### Warranty

**Warranty:** 10-Year Limited

## SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

*\*Leviton is the smart choice, providing the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial buildings. Leveraging more than a century of experience, Leviton helps customers create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, and lighting energy management systems. From switches and receptacles, to daylight harvesting controls, networking systems, and equipment for charging electric vehicles, Leviton solutions help customers achieve savings in energy, time and cost, all while enhancing safety.*

