



GE
Lighting

97622 - GE Ecolux® Blax® T4 - Facilities. Retail Display. Hospitality.

Office. Restaurant. Warehouse

F13TBX/841/A/ECO

Product Photo



GENERAL CHARACTERISTICS

Base Type	Pin/Plug-In
Mercury Content	3 mg
Rated Life Hours-nominal	17000 h
Mercury-Picogram per mean lm hr	233.7
Primary Application	Facilities Retail Display Hospitality Office Restaurant Warehouse
Product Technology	Compact Fluorescent
Base	GX24q-1
Bulb Shape	T4

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	755 lm
Nominal Initial Lumen per Watt	69
Initial Lumens-nominal	900 lm
Color Rendering Index-CRI	82
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	97622
Description	F13TBX/841/A/ECO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168976220
Standard Package GTIN	10043168976227
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168976220
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168976220
Standard Package GTIN	00043168976220
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168976220

DIMENSIONS

Base Face to Top of Lamp	3.7 in
Nominal Length	4.2 in
Bulb Max Overall Length-MOL	4.3 in

ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	60 W
Current Crest Factor (MAX)	5.25
Supply Current Freq nominal Hz	60 Hz
Rated power (Watts)	13 W

CAUTIONS & WARNINGS

Caution

Lamp may shatter and cause injury if broken

Remove and install by grasping only plastic portion of the lamp.