



Specification Sheet

T7 Specialty Incandescent Lamp

Order Number **03720**

Specifications

Energy Used (Watts).....	15
Domestic Code.....	15T7/CB
Volts.....	120
Brightness (Lumens)	108
Average Rated Hours	1000
Life (in years)*	0.9
Dimmable.....	Yes
Filament Type	C5
Light Center Length (LCL)	1 7/16"
Estimated Yearly Energy Cost**	\$1.81
Country of Origin.....	China



Physical Characteristics

Finish	Clear
Base	Candelabra
MOL.....	2 3/16"

* Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee
®“Westinghouse” and “You can be sure...if it’s Westinghouse” are all registered trademarks of Westinghouse Electric Corporation.

