


Steel City[®]



**Recessed Service
T&B Catalog Number:**

664-CST-SW-GRY

UPC Number:

78599103267

Status:

Active

Description:

Recessed Service Floor Box Cover, Length 8-1/8 Inches, Width 5-1/8 Inches, Gray, Polycarbonate with 5/32 Inch Steel Plate

Features

	Factory installed gaskets reduce installation time
	Recessed cover plate accepts tile or carpet to blend into existing floor.
	Dust gasket on the cord shields the floor box from dust and debris.
	Lid snaps securely shut and does not require a locking screw
	Cord can be locked in the open position to protect power and data cables.

Application

For use with 664 and AFM 2 series floor boxes

General

Custom_Finish	664cst_sf1
Material	Non-Metallic
Load Rating (lbs)	1,500
Color	Gray
Cover Material	Non-Metallic

Specifications

3dmodel	Available on Website
Product Specification-DOC	Available on Website
Product Specification-PDF	Available on Website

Accessories & Components

Floor Boxes	sf_664seriesbox_all
Covers & Carpet Plates-664 SC & 664 CI	sf_664scci_accessories
Covers & Carpet Plates-664 S	sf_664s_accessories

Competitor Cross Reference

Competitive Cross Reference Guide	Available on Website
-----------------------------------	----------------------

Packaging

T&B Inner Pack	1
Package in Units	4
T&B Sold in UOM	Each
T&B Weight Per UOM	115 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000057
T&B Instruction Sheets	ta02623-tb2
Product Brochure - Brass & Aluminum	Available on Website
Floor Box Covers	
Floor Box Selection Guide	Available on Website

Product Brochure - MopTite Covers

Available on Website

Notes

*Note

MopTite™ Covers exceed UL watertight requirements for 514A, 514C.

Certifications



File Nbr:

E 2969

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com