



Search: [PRODUCT](#) | [SALES REPRESENTATIVE](#) | [CROSS REFERENCE](#)

Enter a Catalog Number, UPC or Keyword



[Catalog or Sample](#) | [Contact Us](#)

[Home](#)

Product Catalog > Grounding Fittings > Mighty-Bond® Enclosure Grounding and Raceway Bonding Couplings Available in 1/2", 3/4" and 1" Trade Sizes > **MCC-100**


[Print Product Specification Sheet](#) [Email Product Specification Sheet](#)

Category:	Grounding Fittings
Catalog ID:	MCC-100
UPC Number:	78174702342
Description:	Mighty-Bond 1" Brass Equipment Bonding Connector/Coupling
Application:	Used for bonding boxes, devices and enclosures with a minimum wall thickness of 0.1 inches max 0.385 inches to a continuous length of equipment grounding conductor. Installs in a 1" trade size K.O. and can be installed connected to a raceway provided the locknut is still utilized.
Trade Size:	1"
Knockout Size in Inches:	1
Cable Size:	Copper: Stranded 1/0 AWG to 250 MCM. Aluminum: Compact Strand 3/0 to 4/0 AWG
Material:	Brass
Product Note:	A torque of 100 in lbs. is required for 1/0 Str. Copper
Certifications & Codes:	
NEMA Standard:	FB-1
UL Standard:	UL467
UL File Number:	E20412
UNSPSC:	39121613

Patent Number: 7,927,157; D657,316

Dimensions in Inches:
Dimension A in Inches: 1.13
Dimension B in Inches: 1.88
Dimension C in Inches: .56
Dimension D in Inches: .62

Images:



[Download Photo Image](#)

[Download Dimensional Image](#)



Copyright © 2011 Bridgeport Fittings. All Rights Reserved.

Connect Online