



Item #: <b>WC210</b>	UPC Code:
Product Family Name:	Finish:
Category:	Category Type: <b>Accessory</b>
Certification:	
Patents:	
Notes:	



Image File Name:  
WC210--  
1377188413.jpg



## MEASUREMENTS

Width:	Length:	Height:	Extension:
Height Adjustable: <b>No</b>	Min Overall Height:	Max Overall Height:	Slope: <b>No</b>
Wire Length:	Chain Length:	Safety Cable Included <b>No</b>	Net Weight <b>0.52</b>
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

## LAMPING

No. of Bulbs:	Light Type:			
Max Bulb Wattage:	Socket:			
Dimmable: <b>No</b>	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included: <b>No</b>
Lamp Included: <b>No</b>	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

## SHADE / GLASS

Description:	Material:	
Part No.:	Quantity:	
Width:	Height:	Length:



## SHIPPING

Carton Width:	Carton Height:	Carton Length:	
Carton Weight:	Carton Cubit Feet:	Small Package Shippable: <b>No</b>	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties