



8592-965: One Light Outdoor Wall Lantern



Collection: New Castle

Simple Details Create Stylish Outdoor Wall Lantern. Antique Brushed Nickel Finish and Clear Glass.

Simple details create a stylish outdoor wall lantern. Antique brushed nickel finish and clear glass.

UPC #:785652085963

Finish: Antique Brushed Nickel (965)

Dimensions:

Width: 4 1/4" **Extends:** 5 1/2"
Height: 8 1/4" **Wire:** 6 1/2" (color/Black/White)
Weight: 1.4 lbs. **Mounting Proc.:** Cap Nuts
Connection: Mounted To Box
Bulb Appearance: Clear

Bulbs:

1 - Medium A19 100w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Aluminum - Antique Brushed Nickel
 1 Canopy - Aluminum - Antique Brushed Nickel

Safety Listing:

Safety Listed for Wet Locations
 Safety Listed for Wet Locations

Instruction Sheets:

English (HC-231)
 French (F-009)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear	4	G500052-32		3 3/8	4 5/16					

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate			2 1/16	4 1/2	2 3/4	5 1/2

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8592-965	1	785652085963	6.5	4.75	9	0.161	1.5	100	Yes
Master Pack		6	10785652085960	15.5	13.5	9.75	1.181	9.9	100	Yes
NJ Pallet		378		48	40	72	80	523.7		No
NV Pallet		360		48	40	62	68.889	680		No