

Item no.: 222-413  
 Product description: Compact connector 3-conductor terminal blocks with levers  
 max. continuous service temperature 85°C



Produkt kann von Bild abweichen / product may differ

Packing unit 500 pieces

RoHS compliant

Product group	7 (Push Wire Conn.)
Cross section [mm <sup>2</sup> ]	0.08 - 2.5 mm <sup>2</sup>
Cross section [AWG]	28 - 14 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®CONNECTION
Cross section [mm <sup>2</sup> ]	0.08 - 4 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Wiring method	f
Measured voltage EN	400 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	32 A
Weight	4.153 g
Color	grey
Wiring type	Side-entry
No. of connection Points	3
No. of potentials	1
Height	14.5 mm
Height	0.571 in

Width  
Width  
Depth

17 mm  
0.669 in  
20.5 mm



Depth	0.807 in
Strip length from	9 mm
Strip length to	10 mm
Strip length	0.37 in
Customs Tariff No.	85369010
Country of Origin	Deutschland



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
222-413	ABS	10-HN17750340X	450	32	0,5-4
222-413	cULus listed	E69654	600	20	28-12
222-413	ENEC15	DK140137-01	450	32	0,5-4
222-413	PSE	JET0695-43040-1001	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected