



Catalog No. AEU3182RCXAXB4

Description: PRO-STK 480V 3PH 225A NF 18CR CU

UPC No 783175408740

Products > Panelboards > A-Series > Pro-Stock Lighting Panel

- Maximum system voltage is upto 480Vac for AE panelboard line
- Field installable kits allow you to shift gears on the fly
- Standard Pro-Stock panels have the capability of adding sub-feed breakers or feed-thru lugs in the field
- All panel are convertible between main lugs or main breakers
- Reversible interior. No need to specify top or bottom feed
- Solid-state Spectra RMS or thermal magnetic breakers available as mains or sub-feeds
- NEMA 1 or 3R/12 enclosures available
- Flush or surface mounted trims with door within door and front hinge to box options available
- Extruded split neutrals speed and simplify wiring
- Main bus ratings of 225, 400 and 480 amps available
- Modular kits allow for field installation of 200% neutrals and Service Entrance bonding straps
- Field installable TVSS (Transient Voltage Surge Suppression) kits - 200ka per phase
- Up to six poles of sub-feed available in 400A and 600A, and up to 3 poles of sub-feed available in 225A
- Meets all UL, NEMA and CSA standards

Representative Image

Descriptors

| | |
|-------------|--------------------------|
| Category | Pro-Stock Lighting Panel |
| GO Schedule | 32 |

Specifications

| | |
|----------------------|-------------------------------------|
| Voltage | 480 V |
| Phase | 3 |
| Panel Rating | 225 |
| No of Circuits | 18 |
| Feed Thru | No |
| Bus | Copper |
| Interior Type | AEU |
| Box/Front Height | 31.5 in |
| Interior Description | Pro-Stock 480V, 3PH, 225A 18Cir. CU |
| GSA Compliance | No |