



Type			
	-09	-15	-74
P3027	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
P3028	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
P3029	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

Catalog No.	Finish			Lamping	Dimensions (Inches)			
	Brushed Nickel	Polished Chrome	Venetian Bronze		A	B	C	D
P3027	-09	-15	-74	1 (m) 100w	5-5/8	8-1/2	7-1/4	4-3/4
P3028	-09	-15	-74	2 (m) 100w	16-5/8	8-1/2	7-1/4	4-3/4
P3029	-09	-15	-74	3 (m) 100w	24-1/2	8-1/2	7-1/4	4-3/4



P3027



P3029

Specifications:

General

- White opal glass shades: 5-9/16" dia., 5-1/2" ht., 1-5/8" dia. center hole
- Plated Brushed Nickel (-09) and Polished Chrome (-15) finishes
- Venetian Bronze (-74) is a plated finish with hand relieved highlights
- Styled to match Delta Faucet's Victorian Collection
- Turned details on support bar for P3028 and P3029
- Heavy solid brass cast wall plate
- No exposed fasteners to hold glass shades in place

Mounting

- Wall mounted
- Back plate covers a standard 4" hexagonal recessed outlet box: 4-1/2"W., 7-1/16"ht.
- Mounting strap for outlet box included
- Can be mounted in "up or down" position

Electrical

- Medium base ceramic sockets
- Nickel plated brass screw shells
- Threaded socket ring secures glass
- 6" of wire
- Pre-wired

Labeling

- UL-CUL Damp location listed