



# S3952

60A19/F/VS  
60 watt A19 Incandescent; Frost; 2500 average rated hours;  
580 lumens; Medium base; 130 volts; 2/Pack

### Features

- General Service Incandescent
- Household or Commercial use
- Vibration Service
- Long Life
- 130 volt



S3952

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3952	045923039522	60	A19	Medium	E26	60A19/F/VS	130
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost	4 1/8"	2.38"	C-9	580	2500	120	2pk
Dimmable/Non-Dimmable				RoHS Compliant			
Dimmable				Yes			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

