


| |
|--------------|
| Type |
| Project |
| Catalog No. |
| Lamp/Wattage |

NL-3326

Frosted Flat Lens with Reflector

TRIM DIMENSIONS



Trim OD: 3-5/8"
Height: 1-5/8"

FEATURES

Trim
Precision spun 0.050 aluminum high grade specular reflector that includes a frosted flat lens. Gimbal ring allows lamp to be mounted on top of the trim and adjustable up to 35°.

Mounting
Trim includes three trim clips that securely mount trim in housing.

Compatible Housings
Compatible with Line Voltage and Low Voltage housings. See individual specification sheets for more information.

Lamp
Line Voltage
35W 120V MR16 GU10 Max. (NH-350AT; NHIC-350AT; NHR-354AT)
Low Voltage
IMPORTANT: DO NOT USE GLASS LENS (PROVIDED) WHEN ALREADY USING LAMP WITH GLASS COVER
20W-35W 12V MR16 (NL-301 Series; NLIC-301 Series; NLR-304 Series)

Labels and Listings
cULus Listed for Wet Location when used with compatible housing.

Compatible Housings

| LINE VOLTAGE | | | |
|----------------|---------------------------------|----------|--------------------------------|
| Item Number | Installation Type | Lamp | Dimensions |
| NH-350AT | Non-IC Air-Tight New Const. | 35W MR16 | W: 6-3/8" L: 16" H: 5-5/8" |
| NHIC-350AT | IC Air-Tight New Construction | 35W MR16 | W: 6-3/8" L: 16" H: 8-1/8" |
| NHR-354AT | Non-IC Air-Tight Remodel | 35W MR16 | W: 4-1/4" L: 11-1/4" H: 5-5/8" |
| LOW VOLTAGE | | | |
| NL-301QAT/20 | Non-IC AT New Const., Mag. | 20W MR16 | W: 6-3/8" L: 16" H: 5-5/8" |
| NL-301QAT/37 | Non-IC AT New Const., Mag. | 35W MR16 | W: 6-3/8" L: 16" H: 5-5/8" |
| NL-301QAT | Non-IC AT New Const., Mag. | 35W MR16 | W: 6-3/8" L: 16" H: 5-5/8" |
| NL-301AT/1EL | Non-IC AT New Const., Elec. | 35W MR16 | W: 6-3/8" L: 16" H: 5-5/8" |
| NLIC-301QAT/20 | IC Air-Tight New Const., Mag. | 20W MR16 | W: 6-3/8" L: 16" H: 8-1/8" |
| NLIC-301QAT/37 | IC Air-Tight New Const., Mag. | 35W MR16 | W: 6-3/8" L: 16" H: 8-1/8" |
| NLIC-301QAT | IC Air-Tight New Const., Mag. | 35W MR16 | W: 6-3/8" L: 16" H: 8-1/8" |
| NLIC-301AT/1EL | IC Air-Tight New Const., Elec. | 35W MR16 | W: 6-3/8" L: 16" H: 8-1/8" |
| NLR-304QAT/20 | Non-IC Air-Tight Remodel, Mag. | 20W MR16 | W: 4-1/4" L: 11-1/4" H: 5-5/8" |
| NLR-304QAT/37 | Non-IC Air-Tight Remodel, Mag. | 35W MR16 | W: 4-1/4" L: 11-1/4" H: 5-5/8" |
| NLR-304QAT | Non-IC Air-Tight Remodel, Mag. | 35W MR16 | W: 4-1/4" L: 11-1/4" H: 5-5/8" |
| NLR-304AT/1EL | Non-IC Air-Tight Remodel, Elec. | 35W MR16 | W: 4-1/4" L: 11-1/4" H: 5-5/8" |

Frosted Flat Lens with Reflector

- NL-3326B: Frosted Flat Lens with Specular Clear Reflector and Black Metal Ring
- NL-3326BZ: Frosted Flat Lens with Specular Clear Reflector and Bronze Metal Ring
- NL-3326C: Frosted Flat Lens with Specular Clear Reflector and Chrome Metal Ring
- NL-3326CO: Frosted Flat Lens with Specular Clear Reflector and Copper Metal Ring
- NL-3326G: Frosted Flat Lens with Specular Clear Reflector and Gold Metal Ring
- NL-3326N: Frosted Flat Lens with Specular Clear Reflector and Natural Metal Ring
- NL-3326W: Frosted Flat Lens with Specular Clear Reflector and White Metal Ring