

Q40 G9 PIN FROST 120V 12PK SUNLITE



Sunlite 40 Watt, Single Ended T3.5, G9 Bi-Pin Base, Clear

Sunlite Halogen bulbs produce more lumens per-watt (LPW) and have a longer lamp life than standard incandescent lamps. You can lower operation costs by more than 30% by using fewer halogen lamps to produce a greater amount of light. These G9 Bi-Pin Based bulbs can last up to 1.8 years with normal household use of 3 hours a day and display a brighter, whiter light than incandescent bulbs. This Sunlite 40-watt, G9 Bi-Pin Based bulb offers 350 lumens of brightness, a frost glass finish and has an average rated life of 2000 hours. Great for portable lamps, ceiling fixtures, track lighting, showcase displays and most common lighting needs.

- 40-Watt, 400 Lumens
- 2,000 Hour Average Lamp Life
- GY8 base
- Frosted glass, UV protected
- Q40/G9/FR/120V

General Characteristics

Bulb	Bi-Pin
Lamp Type	Single Ended T3.5
Lamp Life Hours	2,000 Hours
Bulb Finish	Frost
Base	Bi-Pin (G9)
Lumens Per Watt (LPW)	8.75
Life (based on 3hr/day)	1.8 Years
Estimated Energy Cost	\$4.82 per Year
Dimmable	True

Electrical Characteristics

Watts	40
Volts	120

Light Characteristics

Brightness	350 Lumens
Color Accuracy (CRI)	100
Light Appearance	Bright White
Color Temperature	3200K

Product Dimensions

MOL (in)	1.568"
Diameter (in)	0.518"
Item Dimensions (in)	(W) 0.52 (H) 1.57 (D) 0.52
Package Dimensions (in)	(W) 0.90 (H) 0.90 (D) 2.80

Product Data

Item Number	66075-SU
Case Quantity	12
Barcode on SKU	653703660752
Barcode on Case	10653703660759
Brand	SUNLITE
Description	Q40/FR/G9/120V

