



Item #: F532-ORB	UPC Code: 706411044069
Product Family Name: Sunseeker	Finish: Oil Rubbed Bronze
Category: Exterior Fan	Category Type: Ceiling Fan
Certification E75795	
Patents	
Notes:	

Image File Name:
F532-ORB_0.jpg



MEASUREMENTS

Blade Finish:	Reversible Blades:	
	No	
Blade Material:	Slope:	
ABS Construction	No	
Blade Sweep:	No. of Blades:	Blade Pitch:
60	5	14
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:
3.5	.75	6
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:
13.75	13.50	80
		Hanging Weight:
		28.06
		Downrod 2 Outside Dia:
		.75
		Motor Size:
		188x25mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	50		85		135
Amps:	0.23		0.39		0.56
Watts:	11.300		31.800		65.100
CFM:	2866.00		4779.00		6783.00
CFM/Watts	253.63		150.28		104.19



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
Yes	Yes	Yes
	Included Remote Control:	Included Wall Control:
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	RCS223,RCS213	WCS223, WC106-WH, WCS213

LAMPING

No. of Bulbs:	Light Type:			
	N/A			
Max Bulb Wattage:	Socket:			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
No	No			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				

GLASS

Description:	Material:	
Part No.:	Quantity:	
Width:	Height:	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
16.500	11.250	24.880	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
31.812	2.673	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
			1



ENERGY STAR
Yes



Wet Location
Yes



Title 17
Yes



UL Listed
Yes