



FM228BS/PN: 2 - Light Indoor Flush Mount

Dimensions:

Diameter: 12 1/2" **Wire:** 8"
Height: 4 1/2" **Connection:** Mounted To Box
Weight: 17.4 lbs.

Bulbs:

2 - Medium A19 60w Max. 120v - Not included

Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
-

Material List:

Safety Listing:

Safety Listed for Dry Locations
 Safety Listed for Dry Locations

Instruction Sheets:

English (FM228)



Collection: Gravity

UPC #: 014817259834

Finish: Brushed Steel / Polished Nickel (BS/PN)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Bowl	Etched Glass	White Opal Etched	1									

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	FM228BS/PN	1	014817259834	16	16.25	8.25	1.241	8.7	125	Yes
Master Pack	FM228BS/PN	2	10014817259831	16	16.25	16.5	2.483	17.4	125	Yes
Shipping Master		2		16	16.25	16.5	2.483	17.4		Yes
NJ Pallet		48		48	40	70	77.778	417.6		No
NV Pallet		48		48	40	70	77.778	417.6		No

Feiss reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Feiss. In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Feiss 1/2 A Generation Brands Company.

