



GE
Lighting

90160 - GE LED PAR38

LED18DP38W830/40

Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Lamp Type	LED-PAR
Primary Application	Indoor and outdoor Floodlight
Rated Life (Hours)	25000 h
Bulb Shape	PAR38

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	2400 cd
Lumens per Watt (Efficacy)	72.2 lm
Nominal Initial Lumen per Watt	72
Rated Beam Spread	40 rad
Initial Lumens-nominal	1300 lm
Color Rendering Index-CRI	84
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	90160
Description	LED18DP38W830/40
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168901604
Standard Package GTIN	10043168901601
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168901604
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168901604
Standard Package GTIN	00043168901604
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168901604

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	18 W