



*Hoffman*

## Panels for Type 3R, 4, 4X, 12 and 13 Enclosures

Catalog Number: A24P24  
US List Price (USD): \$77.56

### Bulletin Number:

- PNLWM

### Material:

- Steel



### Model Code:

- 23180

### Ship Wt. Std. Pkg. (lbs):

- 14.0

### Interchangeable:

- False

### Material:

- Painted steel

## Description

---

### Description:

Steel panels are 12 gauge, finished with white polyester powder paint or a conductive, corrosion-resistant coating. Larger panels have flanges on two or four sides. Some larger steel panels are 10 gauge and include extra holes for panel lifting. Aluminum panels are 5052-H32 aluminum alloy. Larger panels have flanges on four sides. Aluminum panels are protected on one side with a plastic film. Stainless steel panels are Type 316 stainless steel. Panel mounting hardware is furnished with all enclosures which accept these panels.

## Technical Data

---

### Panels for Type 3R, 4, 4X, 12 and 13 Enclosures

<b>Catalog Number</b>	<a href="#">A24P24</a>
<b>A in.</b>	21
<b>B in.</b>	21
<b>Panel Size D x E in.</b>	21.00 x 21.00
<b>Number of Holes</b>	4
<b>Panel Gauge or Thickness</b>	12 ga.
<b>Edge Flanges</b>	2
<b>T in.</b>	0.75

## Certifications

---



EU Certification

## Documents

---



2D DXF CAD



3D STEP CAD



Spec Sheet



Dimension Drawing



Dimension Drawing



Dimension Drawing

No accessories available.