




PRODUCT SPECIFICATION

CATALOG NUMBER: See table below
DESCRIPTION: SJTW replacement power supply cords
APPROVALS: UL / CUL Listed

CONSTRUCTION PARAMETERS:

Conductors: See table below
 Conductor O.D. (nom): See table below
 Insulated conductor O.D. (nom): See table below
 Insulation material: PVC
 Insulation colors: Black White Green
 Overall cable O.D. (nom): See table below
 Jacket material: PVC, black



Note: Plug style may vary

Attachment plug configuration: NEMA 5-15P
 Plug material: PVC, black
 Open end configuration: 1-1/2" ROJ, 3/8" conductor strip

ELECTRICAL PROPERTIES:

Cable temperature rating: -40 to +60 °C
 Nominal operating voltage: 125 VAC
 Maximum operating current: See table below

CATALOG NUMBERS:

Catalog number	Length	Conductor	Conductor O.D.	Insulated conductor O.D.	Overall cable O.D.	Maximum current
09703	3 ft	16/3, 26x30 bare copper	0.059 in	0.120 in	0.330 in	13 A
09706	6 ft					
09709	9 ft					
09716	6 ft	14/3, 41x30 bare copper	0.074 in	0.136 in	0.370 in	15 A
09719	9 ft					

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Inc. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Inc.