



GE
Lighting

97561 - GE Ecolux® Blax® T4 - Facilities. Retail Display. Hospitality.

Office. Restaurant. Warehouse

F9BX/841/ECO

Product Photo



GENERAL CHARACTERISTICS

Base Type	Pin/Plug-In
Mercury Content	3 mg
Rated Life Hours-nominal	10000 h
Starting Temp (MIN) C-degrees	-18 °C
Mercury-Picogram per mean lm hr	600
Primary Application	Facilities Retail Display Hospitality Office Restaurant Warehouse
Product Technology	Compact Fluorescent
Base	G23
Bulb Shape	T4

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	500 lm
Nominal Initial Lumen per Watt	67
Initial Lumens-nominal	600 lm
Color Rendering Index-CRI	82
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	97561
Description	F9BX/841/ECO
Alternative Unit Of Measure	PACK
Standard Package Quantity	
Ean UPC	043168975612
Standard Package GTIN	30043168975613
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Inner Pack
UCC	043168975612
Alternative Unit Of Measure	EACH
Standard Package Quantity	
Ean UPC	043168975612
Standard Package GTIN	00043168975612
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	
Sales Unit	Each
UCC	043168975612

DIMENSIONS

Base Face to Top of Lamp	5.67 in
Nominal Length	6.6 in
Bulb Max Overall Length-MOL	6.59 in

ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	30 W
Supply Current Freq nominal Hz	60 Hz
Input Voltage [nom]	9 V
Rated power (Watts)	9 W

CAUTIONS & WARNINGS

Caution

Lamp may shatter and cause injury if broken

Remove and install by grasping only plastic portion of the lamp.

NOTES

Based on 60Hz reference circuit.