



## 3300-SS



VIDEO

### Product Description

Three gang electrical box for use with nonmetallic sheathed cable

**Brand:** fiberglassBOX™  
**Catalog #:** 3300-SS

**Carton Quantity:** 20  
**Carton Weight:** 16 lb.

**Height:** 3-3/4 in.  
**Width:** 5-11/16 in.  
**Depth:** 3 in.  
**Volume:** 46 cu. in.  
**Type of Installation:** New Work  
**Wall Box**  
**Number of Gangs:** 3

**UPC:** 085339145226  
**UNSPSC:** 39121308  
**Country of Origin:** United States of America

### FEATURES

Machine tapped device holes, offset gauge marks, leveling ribs, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures, Speed "K" Clamps bulk packed

### APPLICATION

New work residential construction - steel or wood studs 2 HR fire resistive walls

### STANDARDS

ANSI / UL 514C: File No. E30594



### FIRE CLASSIFICATION

#### Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

#### Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)

### COLOR

Beige/tan

### MATERIAL

Fiberglass reinforced polyester BMC

### MOUNTING

Steel stud screws for use with non-load bearing studs 22 gauge or lighter

### ADDITIONAL MATERIALS

Carbon steel fasteners

Polyvinyl chloride clamps