

MINKA-LAVERY®

Item #: 341-84	UPC Code: 747396045962
Product Family Name:	Finish: BRUSHED NICKEL
Category: Wall Sconce	Category Type: Sconce
Certification 3057374	
Patents	
Notes:	



Image File Name:

341-84--
1377125234.jpg



MEASUREMENTS

Width: 6.75	Length: 17.25	Height: 4	Extension: 4
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 5.40
Canopy Width: 4.75	Canopy Height: 9.00	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top: 8.63	Center to Bottom: 8.63

LAMPING

No. of Bulbs: 2	Light Type: A19 Med			
Max Bulb Wattage: 100	Socket: E26 Med			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description: Etched White Glass	Material: Glass
Part No.: G341	Quantity: 1
Width: 4.58	Height: 15.25
	Length:



SHIPPING

Carton Width: 9.250	Carton Height: 7.750	Carton Length: 18.800
Carton Weight: 7.370	Carton Cubic Feet: 0.780	Small Package Shippable: Yes
Master Pack Width: 19.250	Master Pack Height: 16.500	Master Pack Length: 28.750
Master Pack Weight: 46.420	Master Cubic Feet:	Multi-Pack: 1
		Master Pack: 6



ADA
Compliant
Yes



Damp
Location
Yes



Title 17
Yes



ETL Intertek
Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties