

# EMT Conduit Bodies

## Set Screw T Type



### Features

- Set screw T type
- Suitable for use in concrete

### Applications


- Provides access to conductors for pulling, splicing and maintenance

### Standard Material

- Copper free aluminum die cast
- Steel screws

### Standard Finish

- Powder coat



Catalog Number	UPC	Size	Max. Number	Max. Size	Unit Carton	Ship Case	Weight/Case	Inches		
								A	B	C
<b>ET1</b>	20690	<b>1/2"</b>	1	6 AWG	10	100	32	4.720	1.370	2.030
<b>ET2</b>	20700	<b>3/4"</b>	2	6 AWG	10	50	30	5.570	1.625	2.335
<b>ET3</b>	20710	<b>1"</b>	3	6 AWG	5	25	15	6.460	1.900	2.705
<b>ET4</b>	20720	<b>1-1/4"</b>	3	2 AWG	2	10	17	8.528	2.770	3.630
<b>ET5</b>	20730	<b>1-1/2"</b>	3	2 AWG	2	10	19	8.528	2.770	3.630
<b>ET6</b>	20740	<b>2"</b>	3	2/0 AWG	---	2	5	10.831	3.335	3.980
<b>ET7</b>	20781	<b>2-1/2"</b>	3	4/0 AWG	---	1	7	13.500	4.060	5.825
<b>ET8</b>	20782	<b>3"</b>	3	250 MCM	---	1	7	13.500	4.685	5.825
<b>ET9</b>	20783	<b>3-1/2"</b>	3	350 MCM	---	1	9	15.937	5.450	7.060
<b>ET10</b>	20744	<b>4"</b>	4	350 MCM	---	1	9	15.937	5.450	7.060