



Powering Business Worldwide

pe.eaton.com

BR style 1-inch commercial loadcenter

3BR3042L200S

UPC:786676442404

Dimensions:

- **Height:** 39 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main lug
- **Amperage Rating:** 200A
- **Box Size:** G1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Mounting:** Surface
- **Number Of Circuits:** 42
- **Number Of Spaces:** 30
- **Number Of Wires:** Four-wire
- **Phase:** Three-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 208Y/120 or 240V
- **Wire Size:** #1-300 kcmil Cu/Al at 60°C or 75°C

Supporting documents:

- [3-Phase Loadcenter Program](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type BR 3-Phase Loadcenters](#)
- [Dimensional Drawing - BR 1 LOADCENTER,](#)



MAIN LUG ONLY, INDOOR NEMA 1, 120/240
VAC, 3 PHASE

Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.