



5232-782: Two Light Semi-Flush Convertible Pendant



Dimensions:

Diameter:	7 1/4"	Height Flush:	11 1/4"
Height:	12"	Overall Height:	61 1/2"
Weight:	4.1 lbs.	Wire:	144" (color/Brown)
		Chain:	48"
		Mounting Proc.:	Dual Mount
		Connection:	Mounted To Box
		Bulb Appearance:	Clear

Bulbs:

2 - Candelabra Torpedo 40w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Fixture is dual mount and may be installed semi-flush or as a pendant.
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

Collection: Bretton

Two Light Hall Fixture Finished in Heirloom Bronze Finish with Clear Glass Panes All Around. Fixture Can be Mounted Close to Ceiling or as a Pendant.

UPC #:785652523335

Finish: Heirloom Bronze (782)

Material List:

- 1 Body - Steel - Heirloom Bronze
- 1 Candle Cover - Polycarbonate - Ivory
- 1 Chain - Steel - Heirloom Bronze

Safety Listing:

Safety Listed for Dry Locations
Safety Listed for Dry Locations

Instruction Sheets:

English (HC-264)
French (F-005)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear	6			3 7/32	7 1/8					

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1			5		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	5232-782	1	785652523335	9.5	7.5	13.75	0.567	5.15	100	Yes
NJ Pallet		108		48	40	74.25	82.5	556.2		No
NV Pallet		108		48	40	74.25	82.5	556.2		No