



Ty-Rap®

Lashing Tie

T&B Catalog Number:

TY5424PX

UPC Number:

78621088817

Status:

Active

Description:

Lashing Cable Tie, Black Polypropylene for Temperatures up to 110 Degrees Celsius (230 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 610mm (24.02 Inches), Width of 13.2mm (0.52 Inches), Thickness of 1.8mm (0.07 Inches), Tensile Strength Rating of 670 Newtons (150 Pounds)

Features

Chemical exposure directly affects the life of a cable tie making polypropylene ties an ideal choice. Black is usable for outdoor use, too.

General

Material	Weather-Resistant Polypropylene
Color	Black

Dimension Information

Nominal Length (inches)	24
Length (inches)	24
Width (inches)	.500
Max. Wire Bundle Diameter (inches)	4

Specifications

Temperature Rating	-40°F to 185°F
--------------------	----------------

Packaging

T&B Order Multiple	25
T&B Inner Pack	25
Package in Units	250
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	3 lbs. per 100

Application Support

Overview	Available on Website
Material Selection Guide	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com