

Portable In-Line 15A GFCI Outlet Adapter, Manual Reset

1594PC2M



Portable Ground Fault Circuit Interrupter, 2'
Cord 15amp 125volt, Manual Reset

features & benefits

- Durable polycarbonate case withstands hard use.
- In-line has bright, green power indicator light that is on when power is available and is visible from both sides of the GFCI.
- Open neutral protection.
- Optional Turnlok plugs and connectors prevent accidental disconnection.
- Optional tri-cord connector handles up to three loads.
- 10kA short circuit rating.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: Yellow
Type: In-Line Portable

Listing Agencies/Third Party Information

CSA Standard: C22.2 No. 42, 144
CUL Listing No: E42190
cULus: Yes
cUL Standard: Yes
UL Listing No: UL498
UL Listed: Yes
UL Standard: Yes
UN SPS C: 39121614

Dimensions

Length U S: 27.75"

Technical Information

Amps: 15A

NEMA Configuration Number: 5-15P/R

NEMA Rating: Yes

Volts: 125V

Volts A C: 125

Buy American Act Compliance

Country of Origin: CHINA

Buy American Act Status: No