



Powering Business Worldwide

pe.eaton.com

3/4 in Type CH Non-EUSERC Meter Breaker

CHMMB200BTS

UPC:782113682020

Dimensions:

- **Height:** 28.38 IN
- **Length:** 4.94 IN
- **Width:** 13 IN

Weight:30 LB

Warranties:

Specifications:

- **Type:** Meter mains
- **Amperage Rating:** 200A
- **Box Size:** F
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Overhead/underground
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CSR2200
- **Mounting:** Surface mounting
- **Number Of Jaws:** Five-jaws
- **Number Of Sockets:** 1
- **Phase:** Single-phase
- **Security:** Ringless
- **Used With:** Type CH breakers
- **Voltage Rating:** 120/240V
- **Bypass:** Horn bypass

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CHMMB200BTS](#)

Certifications:

- UL Listed



Product compliance: No Data

© 2016 Eaton. All rights reserved.